

Set axial EAMM-A-L95-160G-G2

Numar piesa: 8197453

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	112 mm...112 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min...4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...-25 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...-10 °C
Momentul de inertie al masei	430 kgmm ²
Cuplu transmisibil	200 Nm
Greutate produs	6264 g...6264 g
Cod de interfata actuator	L95
Codul interfetei motor In	160G
Nota privind materialele	Conform RoHS