

# Actuator cu piston DFPK-75-20-T32-V4

Numar piesa: 8198977

FESTO



## Fisa de date

Caracteristica	Valoare
Dimensiunea mecanismului de reglare	75
Cursa	20 mm
Pozitie de instalare	orice
Detectarea pozitiei	cu afisaj mecanic
Functie de comanda	inchis prin forta arcului, NC
Presiune de lucru	0.5 MPa...1 MPa 5 bar...10 bar 72.5 psi...145 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-10 °C...60 °C
Tip de protectie	IP65 IP67
Temperatura ambianta	0 °C...60 °C
Greutate produs	2746 g
Conexiune pneumatica	Filet interior G1/8
Nota privind materialele	Conform RoHS
Material capac	Otel inoxidabil turnat
Material garnituri	FPM
Material carcasa	Otel inoxidabil turnat
Cod material carcasa	1.4408
Material tija de piston	otel inoxidabil aliaj inalt