

Bac de gripper HAMA-GA-B33-40-2-S-40-BU

Numar piesa: 8203480

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Diametrul min. de prindere	30 mm
Diametru max. de prindere	55 mm
Cursa de lucru	0 mm...55 mm
Numarul de degete de gripper	2
Design	pentru grippere
Structura constructiva	forma ajustata angajat prin frecare
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Conformitatea LABS	VDMA24364 zona III
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	0 °C...60 °C
Greutate produs	68 g
Culoare	albastru
Duritate Shore	A 40 +5
Nota privind materialele	Conform RoHS
Material bac de gripper	VMQ (silicon), antistatic