

Bac de gripper HAMA-GA-B33-100-4-S-40-BU

Numar piesa: 8203482

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	100
Diametrul min. de prindere	80 mm
Diametru max. de prindere	110 mm
Cursa de lucru	30 mm...125 mm
Numarul de degete de gripper	4
Design	pentru grippere
Structura constructiva	forma ajustata angajat prin frecare
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Conformitatea LABS	VDMA24364 zona III
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	0 °C...60 °C
Greutate produs	315 g
Culoare	albastru
Duritate Shore	A 40 +5
Nota privind materialele	Conform RoHS
Material bac de gripper	VMQ (silicon), antistatic