

Bac de gripper HAMA-GA-B33-70-3-S-40-BU

Numar piesa: 8203485

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	70
Diametrul min. de prindere	55 mm
Diametru max. de prindere	80 mm
Cursa de lucru	20 mm...90 mm
Numarul de degete de gripper	3
Design	pentru grippere
Structura constructiva	forma ajustata angajat prin frecare
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Conformitatea LABS	VDMA24364 zona III
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	0 °C...60 °C
Greutate produs	114 g
Culoare	albastru
Duritate Shore	A 40 +5
Nota privind materialele	Conform RoHS
Material bac de gripper	VMQ (silicon), antistatic