

Cuplaj EAMC-56-58-25-25-U

Numar piesa: 8203733

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	25 mm
Diametru de montare 2	25 mm
Dimensiune	56
Lungime nominala	58 mm...58 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min...5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...-25 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...-25 °C
Momentul de inertie al masei	128 kgmm ²
Cuplu transmisibil	75 Nm
Greutate produs	266 g...266 g
Nota privind materialele	Conform RoHS