

Unitate de ghidare FEN-25-125-GF

Numar piesa: 8204055

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	25
Cursa	125 mm
Pozitie de instalare	orice
Ghidaj	Ghidaj de alunecare
Structura constructiva	Ghidaj
Protectie la explozie	Respectati informatiile din certificat
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Fora de deplasare	15 N
Masa in miscare	419 g
Greutate produs	1016 g
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	otel aliaj inalt
Material carcasa	Aliaj de aluminiu forjat, anodizat
Material placa de jug	Aliaj de aluminiu forjat, anodizat