

Motorski vod NEBM-S1G15-E-10-Q7-LE6

Broj artikla: 1450838

★ Kernprogramm

odgovara za koračni motor EMMS-ST...

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	10
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	6
Electrical connection 2, occupied pins/wires	6
Područje pogonskog napona DC	0 ... 72 V
Nazivni pogonski napon DC	24 V
Dužina kabla	10 m
Svojstvo kabla	Suitable for energy chains
Bending radius, flexible cable installation	≥ 80 mm
Prečnik kabla	8 mm
Struktura kabla	6x0,75 zaslonjeno
Nazivni presek provodnika	0,75 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-40 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material insulation	PP