


Vod utičnice KMPYE-5

Broj artikla: 151909

FESTO

predgrađeno, za proporcionalni razvodnik.



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61076-2-101
Cable identification	sa priborom
Težina proizvoda	305 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hex A/F 18 mm and longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Dozvoljeno strujno opterećenje	4 A
Čvrstoća na udarno naprezanje	2,5 kV
Dužina kabla	5 m
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, flexible cable installation	≥ 90 mm
Prečnik kabla	6,2 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	4x0,25 zaslonjeno
Nazivni presek provodnika	0,25 mm ²
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-40 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Material cable sheath	PVC
Boja izolacije	sivo
Material housing	PA
Boja kućišta	crno
Material screw-type lock	PA
Material electrical contact	Mesing