

# Prirubno pričvršćenje EAHH-V2-50-R1

Broj artikla: 2827589

FESTO



## Tehnički podaci

| Svojstvo                       | Vrednost   |
|--------------------------------|--|
| Veličina                       | 50   |
| Zasnovano na normi             | ISO 15552  |
| Klasa korozione otpornosti KBK | 3 - High corrosion stress  |
| PWIS conformity                | VDMA24364-B2-L   |
| RSBP classification to CD-0033 | F5a  |
| Cleanroom class                | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Težina proizvoda               | 496 g  |
| Materijal - napomena           | RoHS komfornost  |
| Material plate                 | visokolegirani čelik, nerđajući  |
| Material screws                | visokolegirani čelik, nerđajući  |