


# Spojni vod NEBV-B2W3-K-0.6-N-LE3

Broj artikla: 3579468

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Dozvola	c CSA us (OL)
Cable identification	Without inscription label holder
Težina proizvoda	80 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Plug pattern type B to industry standard, 11 mm
Electrical connection 1, number of pins/wires	3
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	na elektromagnetnom ventilu sa središnjim vijkom M3
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Područje pogonskog napona DC	0 ... 230 V
Nazivni pogonski napon DC	230 V
Područje pogonskog napona AC	0 ... 230 V
Nazivni pogonski napon AC	230 V
Strujna opteretivost kod 40°C	10 A
Čvrstoća na udarno naprezanje	4 kV
Priključak uzemljenja	postoji
Dužina kabla	0,6 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Prečnik kabela	5,9 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	3x0,75
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material insulation	PP