



# Spojni vod NEBV-A1W3F-P-K-0.6-N-LE3

Broj artikla: 3679776

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Dozvola	c CSA us (OL)
Indikacija stanja	LED žuti
Dodatne funkcije	Zaštitni krug
Cable identification	Without inscription label holder
Težina proizvoda	80 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Plug pattern type A based on EN 175301-803
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	na elektromagnetnom ventilu sa središnjim vijkom M3
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Područje pogonskog napona DC	18 ... 30 V
Nazivni pogonski napon DC	24 V
Područje pogonskog napona AC	18 ... 30 V
Nazivni pogonski napon AC	24 V
Strujna opteretivost kod 40°C	4 A
Čvrstoća na udarno naprezanje	0,8 kV
Priključak uzemljenja	postoji
Dužina kabla	0,6 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Prečnik kabla	5,9 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	3x0,75
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material insulation	PP