


Spojni vod

NEBS-SM12G12-E-0.5-N-LE12

Broj artikla: 3947401

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61076-2-101
Cable identification	sa priborom
Frekvencija priključivanja	100
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw locking with hex SW13
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	12
Electrical connection 2, occupied pins/wires	12
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	1,5 A
Čvrstoća na udarno naprezanje	0,5 kV
Dužina kabla	0,5 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 32 mm
Bending radius, flexible cable installation	≥ 65 mm
Prečnik kabela	6,5 mm
Struktura kabla	12x0,25
Nazivni presek provodnika	0,25 mm ²
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-5 ... 70 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 70 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	crno
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated die-cast zinc
Material electrical contact	Brass, gold-plated