


Motorski vod

NEBM-M23G15-EH-2.5-Q7N-R3LEG14

Broj artikla: 5251374

★ Kernprogramm

FESTO



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61984
Cable identification	Without inscription label holder
Težina proizvoda	875 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M23x1
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Plugs and cables
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	RJ45 and open end
Electrical connection 2, number of pins/wires	14
Electrical connection 2, occupied pins/wires	12
Područje pogonskog napona DC	0 ... 850 V
Područje pogonskog napona AC	0 ... 630 V
Strujna opteretivost kod 40°C	11,7 A
Čvrstoća na udarno naprezanje	6 kV
Dužina kabla	2,5 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 48 mm
Bending radius, flexible cable installation	≥ 90 mm
Prečnik kabela	12 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	4 x 0.75 mm ² + 1 x (2 x 0.75 mm ²) + 1 x (2 x 0.24 mm ² + 2 x 2 x 0.15 mm ²) zaslonjeno
Nazivni presek provodnika	0,15 mm ² 0,24 mm ² 0,75 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-40 ... 90 °C
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost Bez halogena
Stepen zagađenja	1
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material insulation	PP