

Priključni kabl KMP6-09P-8-2,5



Broj artikla: 531184

Classic - nicht für Neukonstruktionen verwenden

za minijaturne ventile, sa SubD-utikačem, 9-polni za 8 kalemova.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	DIN 41652
Cable identification	Without inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	248 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	9
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	9
Electrical connection 2, occupied pins/wires	9
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Strujna opteretivost kod 40°C	2,8 A
Čvrstoća na udarno naprezanje	1 kV
Dužina kabla	2,5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 76 mm
Bending radius, flexible cable installation	≥ 114 mm
Prečnik kabla	7,6 mm
Odstupanje prečnika kabla	± 0,25 mm
Struktura kabla	8x0,34+1x0,5
Nazivni presek provodnika	0,34 mm ² 0,5 mm ²
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP40
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 70 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 70 °C
Temperatura ležaja	-25 ... 75 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	2

Svojstvo	Vrednost
Material cable sheath	PVC
Boja izolacije	sivo
Material housing	PBT ojačan
Boja kućišta	sivo
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy