

# Motorski vod


## NEBM-M23G8-E-10-Q9N-LE8-1

Broj artikla: 5391144

Komponenta koja će prestati da se proizvodi

For EMMS-AS-70/100/140 with CMMT-AS.

FESTO



## Tehnički podaci

| Svojstvo   | Vrednost   |
|--|--|
| Odgovara standardu                                   | EN 61984   |
| Cable identification                                 | Without inscription label holder   |
| Težina proizvoda                                     | 2.300 g  |
| Electrical connection 1, function                    | Field device side  |
| Electrical connection 1, design                      | okruglo  |
| Electrical connection 1, connection type             | Utičnica   |
| Electrical connection 1, cable outlet                | Ravno  |
| Electrical connection 1, connection technology       | M23x1  |
| Electrical connection 1, number of pins/wires        | 8  |
| Electrical connection 1, occupied pins/wires         | 8  |
| Electrical connection 2, function                    | Controller side  |
| Electrical connection 2, connection type             | Kabl   |
| Electrical connection 2, connection technology       | otvoreni kraj  |
| Electrical connection 2, number of pins/wires        | 8  |
| Electrical connection 2, occupied pins/wires         | 8  |
| Područje pogonskog napona DC                         | 0 ... 630 V  |
| Note on operating voltage range DC                   | 0 - 300 V for 0.5 mm <sup>2</sup>  |
| Područje pogonskog napona AC                         | 0 ... 630 V  |
| Note on operating voltage range AC                   | 0 - 300 V for 0.5 mm <sup>2</sup>  |
| Strujna opteretivost kod 40°C                        | 16 A   |
| Note on acceptable current load at 40°C              | 8 A for 0.5 mm <sup>2</sup>  |
| Čvrstoća na udarno naprezanje                        | 4 kV   |
| Note on surge resistance                             | 2.5 kV for 0.5 mm <sup>2</sup>   |
| Dužina kabela  | 10 m   |
| Svojstvo kabela                                      | prikladno za energetski lanac  |
| Bending radius, fixed cable installation             | ≥ 60 mm  |
| Bending radius, flexible cable installation          | ≥ 120 mm   |
| Prečnik kabela                                       | 12 mm  |
| Struktura kabela                                     | 4x1,5+2x(2x0,5)<br>zaslonjeno  |
| Nazivni presek provodnika                            | 0,5 mm <sup>2</sup><br>1,5 mm <sup>2</sup>                                   |
| Krajevi žica   | Cable end sleeve to DIN 46228-A..-10<br>Cable end sleeve to DIN 46228-E..-10 |
| Mehanička zaštita                                    | IP65   |
| Note on degree of protection                         | u montiranom stanju  |
| Temperatura okoline                                  | -50 ... 90 °C  |
| Temperatura okoline kod pokretnog postepenja kablova | -40 ... 90 °C  |
| CE znak (vidi izjavu o usklađenosti)                 | prema EU-niski napon-smernica<br>in accordance with EU RoHS directive        |
| UKCA marking (see declaration of conformity)         | To UK instructions for electrical equipment<br>To UK RoHS instructions       |
| PWIS conformity                                      | VDMA24364-B2-L   |
| Materijal - napomena                                 | RoHS komfornost  |
| Stepen zagađenja                                     | 3  |
| Material cable sheath                                | TPE-U(PUR)   |
| Boja izolacije                                       | narandžasto  |