



# Spojni vod NEBU-M8W3N-K-2.5-LE3

Broj artikla: 541336

FESTO

za cilindarske senzore, prenosnici pozicije, pritisne sklopke, senzori protoka, optički i induktivni senzori.



## Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	Core colours and connection numbers to EN 60947-5-2 EN 61076-2-104
Indikacija pogonske spremnosti	LED zeleni
Indikacija stanja	LED žuti za NPN normalno otvoren kontakt
Cable identification	with 2x label holders
Težina proizvoda	64 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	3
Područje pogonskog napona DC	10 ... 30 V
Strujna opteretivost kod 40°C	3 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabla	2,5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Energy chain: > 5 million cycles, bending radius 75 mm
Bending radius, fixed cable installation	12 mm
Bending radius, flexible cable installation	39 mm
Prečnik kabla	3,8 mm
Odstupanje prečnika kabla	± 0,1 mm
Struktura kabla	3x0,25
Nazivni presek provodnika	0,25 mm <sup>2</sup>
Mehanička zaštita	IP65 IP68 IP69K
Note on degree of protection	u montiranom stanju
Posebne karakteristike	postojano na ulje
Temperatura okoline	-25 ... 70 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 70 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive

Svojstvo	Vrednost
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost Bez halogena Free of phosphoric acid ester
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulation	PP