


Spojni vod NEBV-S1W37-KM-10-LE10

Broj artikla: 543273

FESTO

za višepolni priključak na ventilski blok VTSA i VTSA-F, za maks. 8 elektromagnetnih kalemova, sa Sub-D utičnicom, 10-polnom.



Tehnički podaci

Svojstvo	Vrednost
Područje primene	Only for multi-pin plug connection valve terminal VTSA/VTSA-F
Odgovara standardu	DIN 47100
Cable identification	With inscription label holder
Težina proizvoda	907 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	37
Electrical connection 1, occupied pins/wires	10
Electrical connection 1, type of mounting	3x M4 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	10
Electrical connection 2, occupied pins/wires	10
Područje pogonskog napona DC	0 ... 30 V
Strujna opteretivost kod 40°C	2 A
Čvrstoća na udarno naprezanje	1 kV
Dužina kabla	10 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 29 mm
Bending radius, flexible cable installation	≥ 54 mm
Prečnik kabla	7,2 mm
Struktura kabla	10x0,34
Nazivni presek provodnika	0,34 mm ²
Mehanička zaštita	IP65 NEMA 4
Note on degree of protection	u montiranom stanju
Temperatura okoline	-5 ... 50 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	PVC
Boja izolacije	sivo
Material housing	PA
Material insulation	PVC