


# Priključni kabl NEBV-M12G8-K-2-M12G4

Broj artikla: 553575

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61076-2-101
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	okruglo
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw lock
Područje pogonskog napona DC	0 ... 30 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	2 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabla	2 m
Svojstvo kabla	Standard
Bending radius, fixed cable installation	≥ 29 mm
Bending radius, flexible cable installation	≥ 58 mm
Prečnik kabela	5,6 mm
Odstupanje prečnika kabla	± 0,2 mm
Struktura kabla	4x0,34 zaslonjeno
Nazivni presek provodnika	0,34 mm <sup>2</sup>
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 85 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost Bez halogena
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Brass, gold-plated
Material insulation	PP