

Plastično crevo PLN-10X1,5-BL

Broj artikla: 558208

FESTO

visoka postojanost na hemikalije i hidrolizu.



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	10 mm
Radius savijanja, merodavan za protok	57 mm
Unutrašnji prečnik	7 mm
Min. radius savijanja	22 mm
Temperature-dependent operating pressure	-0,095 ... 1,4 MPa
Pogonski pritisak zavisian od temperature	-0,95 ... 14 bar
Temperature-dependent operating pressure	-13,775 ... 203 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 50 °C
Dozvola	TÜV
Mesto izdavanja sertifikata	B 013277 0506 00
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Temperatura okoline	-30 ... 80 °C
Težina proizvoda prema dužini	0,0375 kg/m
Pneumatski priključak	For push-in connector outside diameter 10 mm
Boja	plavo
Materijal - napomena	RoHS komformnost
Material tubing	PE