

Plastično crevo PUN-V0-6X2-RT-C

Broj artikla: 561710

FESTO

nezapaljivo



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	6 mm
Radius savijanja, merodavan za protok	24 mm
Unutrašnji prečnik	2 mm
Min. radius savijanja	7 mm
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 1,6 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 16 bar
Operating pressure for entire temperature range	-13,775 ... 232 psi
Temperature-dependent operating pressure	-0,095 ... 3 MPa
Pogonski pritisak zavisn od temperature	-0,95 ... 30 bar
Temperature-dependent operating pressure	-13,775 ... 435 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at max. 50°C For applications with welding spatter: max. 1 MPa at 20°C, max. 0.9 MPa at 40°C, max. 0.7 MPa at 60°C
Dozvola	TÜV
Mesto izdavanja sertifikata	B 013277 0506 00
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 V-0 (3mm) UL94 V-2 (0,75mm)
PWIS conformity	VDMA24364-B2-L
Temperatura okoline	-35 ... 60 °C
Note on ambient temperature	For unpressurised use up to 90 °C
Težina proizvoda prema dužini	0,032 kg/m
Pneumatski priključak	For push-in connector outside diameter 6 mm for barbed connector internal diameter 2 mm with nut
Boja	crveno
Napomena za boju	odstupanje prema standardnoj boji zbog vatrozaštite
Tvrdoća po Shoreu	D 54 +/-3
Materijal - napomena	RoHS komformnost
Material tubing	TPE-U(PU)