



Motorski vod

NEBM-M12G4-RS-15-N-LE4

Broj artikla: 571907

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	DIN 47100 EN 61984
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw locking with SW14
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 250 V
Područje pogonskog napona AC	0 ... 250 V
Strujna opteretivost kod 40°C	4 A
Dužina kabla	15 m
Svojstvo kabla	prikladno za robot
Bending radius, flexible cable installation	≥ 60 mm
Prečnik kabla	5,9 mm
Struktura kabla	4x0,34 zaslonjeno
Nazivni presek provodnika	0,34 mm ²
Krajevi žica	Završetak žice
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	0 ... 40 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	crno
Material housing	TPE-U(PUR)
Material seals	NBR
Material insulation	TPE-E