


Utični rukavac NPQH-D-S10-E-P10

Broj artikla: 578320

FESTO



Tehnički podaci

Svojstvo	Vrednost
Veličina	Standard
Nazivni prečnik	8 mm
Položaj ugradnje	proizvoljno
Oblik	Ravni oblik
Veličina kontejnera	10
Operating pressure for entire temperature range	-0,095 ... 2 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 20 bar
Operating pressure for entire temperature range	-13,775 ... 290 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 50 °C
Mesto izdavanja sertifikata	NSF C0523185
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Napomena o mediju pogona i upravljanja	Moguć nauljeni pogon
Klasa korozione otpornosti KBK	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See declaration of conformity NSF/ANSI 169
Temperatura okoline	0 ... 150 °C
Težina proizvoda	12 g
Pneumatski priključak 1	Push-in sleeve diameter 10 mm
Pneumatski priključak 2	Push-in sleeve diameter 10 mm
Materijal - napomena	RoHS komformnost
Material housing	Brass, chemically nickel-plated