

Utični priključak NPQH-D-G12-S12-P10

Broj artikla: 578369

FESTO



Tehnički podaci

Svojstvo	Vrednost
Veličina	Standard
Nazivni prečnik	10 mm
Način zaptivanja na navojnom čepu	Zaptivni prsten
Položaj ugradnje	proizvoljno
Oblik	Ravni oblik
Veličina kontejnera	10
Konstruktivna struktura	Push-pull princip
Operating pressure for entire temperature range	-0,095 ... 2 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 20 bar
Operating pressure for entire temperature range	-13,775 ... 290 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 50 °C
Mesto izdavanja sertifikata	NSF C0523185
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Napomena o mediju pogona i upravljanja	Moguć nauljeni pogon
Klasa korozione otpornosti KBK	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See declaration of conformity NSF/ANSI 169
Temperatura okoline	0 ... 150 °C
Nazivni moment pritezanja	9 Nm
Tolerancija uz nazivni moment pritezanja	± 20 %
Težina proizvoda	34 g
Vrsta pričvršćenja	External hexagon A/F 25
Pneumatski priključak 1	Spoljašnji navoj G1/2
Pneumatski priključak 2	Push-in sleeve diameter 12 mm
Materijal - napomena	RoHS komformnost
Material housing	Brass, chemically nickel-plated
Material of threaded seal	FPM