

# Zaptivni vijak NPQH-BK-G18-P10

Broj artikla: 578406

FESTO



## Tehnički podaci

| Svojstvo  | Vrednost   |
|---|--|
| Veličina  | Standard   |
| Način zaptivanja na navojnom čepu                   | Zaptivni prsten  |
| Položaj ugradnje                                    | proizvoljno  |
| Oblik   | Plug screw   |
| Veličina kontejnera                                 | 10   |
| Operating pressure for entire temperature range     | -0,095 ... 2 MPa   |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 20 bar   |
| Operating pressure for entire temperature range     | -13,775 ... 290 psi  |
| Napomena za pogonski pritisak                       | Water: max. 0.6 MPa at 0 - 50 °C   |
| Mesto izdavanja sertifikata                         | NSF C0523185   |
| Pogonski medijum                                    | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-]<br>Water (liquid, free of ice)   |
| Napomena o mediju pogona i upravljanja              | Moguć nauljeni pogon   |
| Klasa korozione otpornosti KBK                      | 3 - High corrosion stress  |
| PWIS conformity                                     | VDMA24364-B1/B2-L  |
| Cleanroom class                                     | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe   | See declaration of conformity<br>NSF/ANSI 169  |
| Temperatura okoline                                 | 0 ... 150 °C   |
| Nazivni moment pritezanja                           | 6 Nm   |
| Tolerancija uz nazivni moment pritezanja            | ± 20 %   |
| Težina proizvoda                                    | 4,4 g  |
| Vrsta pričvršćenja                                  | Internal hex A/F 5   |
| Pneumatski priključak 1                             | Spoljašnji navoj G1/8  |
| Materijal - napomena                                | RoHS komfornost  |
| Material housing                                    | Brass, chemically nickel-plated  |
| Material of threaded seal                           | FPM  |
| Material release ring                               | Brass, chemically nickel-plated  |