


# Plastično crevo PUN-H-1/4-NT-500-HA

Broj artikla: 8003126

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik, col	1/4
Radius savijanja, merodavan za protok	0,085 ft
Min. radius savijanja	0,046 ft
Uputstva za korišćenje	TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Pogonski pritisak zavisao od temperature	-14,4 ... 145 Psi
Napomena za pogonski pritisak	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Temperatura okoline	-31 ... 145 °F
Težina proizvoda prema dužini	0,23 oz/ft
Pneumatski priključak	za utični priključak spoljašnji prečnik 1/4"
Boja	prirodno
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS komfornost
Material tubing	TPE-U(PU)