

# Plastično crevo PTFEN-4X0,5-NT-100

Broj artikla: 8061171

FESTO



## Tehnički podaci

| Svojstvo  | Vrednost   |
|---|--|
| Spoljašnji prečnik                                  | 4 mm   |
| Radius savijanja, merodavan za protok               | 32 mm  |
| Unutrašnji prečnik                                  | 2,9 mm   |
| Min. radius savijanja                               | 32 mm  |
| Uputstva za korišćenje                              | Tubing without printing  |
| Operating pressure for entire temperature range     | -0,095 ... 0,5 MPa   |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 5 bar  |
| Operating pressure for entire temperature range     | -13,775 ... 72,5 psi   |
| Temperature-dependent operating pressure            | -0,095 ... 1,2 MPa   |
| Pogonski pritisak zavisao od temperature            | -0,95 ... 12 bar   |
| Temperature-dependent operating pressure            | -13,775 ... 174 psi  |
| Pogonski medijum                                    | Kompresovani vazduh prema ISO 8573-1:2010 [7::-]   |
| Material fire test                                  | UL94 V-0   |
| PWIS conformity                                     | VDMA24364-B1/B2-L  |
| Cleanroom class                                     | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly.                     |
| Food-safe   | See Supplementary material information   |
| Temperatura okoline                                 | -20 ... 150 °C   |
| Težina proizvoda prema dužini                       | 0,013 kg/m   |
| Pneumatski priključak                               | For push-in connector outside diameter 4 mm<br>For barbed connector outside diameter 4 mm with union nut<br>za spajanje navlačenjem, unutrašnji prečnik 3 mm sa maticom<br>for barbed connector internal diameter 3 mm |
| Boja  | prirodno   |
| Tvrdoća po Shoreu                                   | D 55 +/-5  |
| Materijal - napomena                                | RoHS komformnost   |
| Material tubing                                     | PTFE   |