

Plastično crevo PTFEN-8X1-NT

Broj artikla: 8061173

FESTO



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	8 mm
Radius savijanja, merodavan za protok	90 mm
Unutrašnji prečnik	5,9 mm
Min. radius savijanja	64 mm
Uputstva za korišćenje	Tubing without printing
Operating pressure for entire temperature range	-0,095 ... 0,5 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 5 bar
Operating pressure for entire temperature range	-13,775 ... 72,5 psi
Temperature-dependent operating pressure	-0,095 ... 1,2 MPa
Pogonski pritisak zavisao od temperature	-0,95 ... 12 bar
Temperature-dependent operating pressure	-13,775 ... 174 psi
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7::-]
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B1/B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Temperatura okoline	-20 ... 150 °C
Težina proizvoda prema dužini	0,047 kg/m
Pneumatski priključak	For push-in connector outside diameter 8 mm For barbed connector outside diameter 8 mm with union nut za spajanje navlačenjem, unutrašnji prečnik 6 mm sa maticom for barbed connector internal diameter 6 mm
Boja	prirodno
Tvrdoća po Shoreu	D 55 +/-5
Materijal - napomena	RoHS komformnost
Material tubing	PTFE