


# Spojni vod NEBB-M8W4-P-2.5-LE4

Broj artikla: 8066667

FESTO



## Tehnički podaci

| Svojstvo                                       | Vrednost  |
|--|---|
| Odgovara standardu                             | Core colours and connection numbers to EN 60947-5-2<br>EN 61076-2-104 |
| Cable identification                           | With inscription label holder   |
| Electrical connection 1, function              | Field device side   |
| Electrical connection 1, design                | okruglo   |
| Electrical connection 1, connection type       | Utičnica  |
| Electrical connection 1, cable outlet          | Angled  |
| Electrical connection 1, connection technology | M8x1, A-coded to EN 61076-2-104                                       |
| Electrical connection 1, number of pins/wires  | 4   |
| Electrical connection 1, occupied pins/wires   | 4   |
| Electrical connection 1, type of mounting      | Screw lock with A/F9  |
| Electrical connection 2, function              | Controller side   |
| Electrical connection 2, connection type       | Kabl  |
| Electrical connection 2, connection technology | otvoreni kraj   |
| Electrical connection 2, number of pins/wires  | 4   |
| Electrical connection 2, occupied pins/wires   | 4   |
| Područje pogonskog napona DC                   | 0 ... 30 V  |
| Područje pogonskog napona AC                   | 0 ... 30 V  |
| Strujna opteretivost kod 40°C                  | 4 A   |
| Čvrstoća na udarno naprezanje                  | 0,8 kV  |
| Dužina kabla                                   | 2,5 m   |
| Svojstvo kabla                                 | Za statičke namene  |
| Uslovi ispitivanja kabla                       | Uslovi ispitivanja na zahtev  |
| Bending radius, fixed cable installation       | ≥ 14 mm   |
| Prečnik kabla                                  | 4,5 mm  |
| Struktura kabla                                | 4x0,25  |
| Nazivni presek provodnika                      | 0,25 mm <sup>2</sup>  |
| Krajevi žica                                   | Sheath removed<br>Cut off bluntly                                     |
| Mehanička zaštita                              | IP65<br>IP68<br>IP69K   |
| Note on degree of protection                   | u montiranom stanju   |
| Temperatura okoline                            | -25 ... 70 °C   |
| CE znak (vidi izjavu o usklađenosti)           | in accordance with EU RoHS directive                                  |
| UKCA marking (see declaration of conformity)   | To UK RoHS instructions   |
| PWIS conformity                                | VDMA24364-B2-L  |
| Cleanroom class                                | ISO class 4   |
| Materijal - napomena                           | RoHS komformnost  |
| Stepen zagađenja                               | 3   |
| Klasa korozione otpornosti KBK                 | 2 - Moderate corrosion stress   |
| Material cable sheath                          | PVC   |
| Boja izolacije                                 | sivo  |
| Material housing                               | TPE-U(PU)   |
| Boja kućišta                                   | crno  |
| Material screw-type lock                       | Nickel-plated brass   |
| Material seals                                 | NBR   |
| Material electrical contact                    | Gold-plated copper alloy  |
| Material insulation                            | PVC   |