


Vod enkodera NEBM-T1G8-E- -N-R3G8

Broj artikla: 8085947

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Težina proizvoda	79 ... 1.255 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	ITT M3
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	RJ45
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Područje pogonskog napona AC	0 ... 30 V
Nazivni pogonski napon AC	24 V
Dužina kabela	1 ... 25 m
Svojstvo kabela	prikladno za energetska lanac
Bending radius, flexible cable installation	≥ 48 mm
Prečnik kabela	5,8 mm
Struktura kabela	1x4x0,15+4x0,34 zaslonjeno
Nazivni presek provodnika	0,15 mm ² 0,34 mm ²
Mehanička zaštita	IP65
Note on degree of protection	IP30 for plug connector Sub-D u montiranom stanju
Temperatura okoline	-40 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-10 ... 80 °C
CE znak (vidi izjavu u usklađenosti)	in accordance with EU RoHS directive
Materijal - napomena	RoHS komfornost
Material cable sheath	TPE-U(PUR)