

# Sigurnosna kopča NPAP-QE-S-Q12-P10

Broj artikla: 8113232

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Veličina kontejnera	10
Položaj ugradnje	proizvoljno
Operating pressure for entire temperature range	-0,095 ... 0,8 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 8 bar
Operating pressure for entire temperature range	-13,775 ... 116 psi
Klasa korozione otpornosti KBK	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-5 ... 60 °C
Težina proizvoda	0,28 g
Pneumatski priključak	za crevo spoljašnjeg prečnika 12 mm
Materijal - napomena	RoHS komformnost