

Plastično crevo PUN-H-F-14X2-BL

Broj artikla: 8153417

FESTO



Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	14 mm
Radijus savijanja, merodavan za protok	78 mm
Unutrašnji prečnik	9,8 mm
Min. radijus savijanja	38 mm
Uputstva za korišćenje	Tubing without printing TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1 MPa
Pogonski pritisak zavisn od temperature	-0,95 ... 10 bar
Temperature-dependent operating pressure	-13,775 ... 145 psi
Napomena za pogonski pritisak	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See declaration of conformity
Temperatura okoline	-35 ... 60 °C
Težina proizvoda prema dužini	0,0911 kg/m
Pneumatski priključak	For push-in connector outside diameter 14 mm
Boja	plavo
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS komformnost
Material tubing	TPE-U(PU)