

Plastično crevo PUN-H-F-8X1,25-NT

Broj artikla: 8153429

FESTO

Ovaj proizvod se može koristiti sa priključcima serije: QS, NPQP, NPQM, CRQS i CK.



Tehnički podaci

| Svojstvo | Vrednost |
|---|--|
| Spoljašnji prečnik | 8 mm |
| Radius savijanja, merodavan za protok | 37 mm |
| Unutrašnji prečnik | 5,7 mm |
| Min. radius savijanja | 21 mm |
| Uputstva za korišćenje | Tubing without printing TPE-U Ether basiert |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0,095 ... 0,6 MPa |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 6 bar |
| Operating pressure for entire temperature range | -13,775 ... 87 psi |
| Temperature-dependent operating pressure | -0,095 ... 1 MPa |
| Pogonski pritisak zavisian od temperature | -0,95 ... 10 bar |
| Temperature-dependent operating pressure | -13,775 ... 145 psi |
| Napomena za pogonski pritisak | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C |
| Pogonski medijum | Kompresovani vazduh prema ISO 8573-1:2010 [7::-] Oxygen Water (liquid, free of ice) |
| Material fire test | UL94 HB |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe | See declaration of conformity |
| Temperatura okoline | -35 ... 60 °C |
| Težina proizvoda prema dužini | 0,0285 kg/m |
| Pneumatski priključak | For push-in connector outside diameter 8 mm za spajanje navlačenjem, unutrašnji prečnik 6 mm sa maticom |
| Boja | prirodno |
| Tvrdoća po Shoreu | D 52 +/-3 |
| Materijal - napomena | RoHS komformnost |
| Material tubing | TPE-U(PU) |