


Kumanda FEC-FC640-FST

Ürün numarası: 191450

FESTO

FEC Standard 32 giriş / 16-transistör-çıkış, 24 V DC, Ethernet 10BaseT, FST. Ağa için alüminyum gövdeli kumanda birimi, çabuk bağlantılı sistem, 2 seri arabirim, bütün bağlantılar ön taraftan.

Products to be discontinued. Available until 2010.



Bilgi sayfası

Özellik	Değer
Müsaade edilebilirlik	C-Tick
Operating voltage	24 VDC +25% / -15%
Current consumption	24 VDC 'de nominal olarak 200 mA
Power supply cable length	10 m
Çevre sıcaklığı	0 ... 55 °C
Depolama sıcaklığı	-25 ... 70 °C
Relatif hava nemi	95% yoğunlaşmayan
Koruma sınıfı	IP20 III
Ürün ağırlığı	500 g
Test for insensitivity to vibration	EN 60068-2-6-FC 10-57 Hz 0,075 mm 57 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15g, 11ms 2 Şok/Yön
Run/Stop switch	evet
Elektriksel bağlantı teknolojisi G/Ç	Tension-spring system
Status displays	LED
Digital inputs, number	32
Digital inputs, fast counting inputs	2, her defasında maksimum 2 kHz
Digital inputs, incremental encoder connection	Yes, max. 200 Hz
Digital inputs, input signal delay	5 ms typ.
Digital inputs, input voltage/current	24 VDC / 5 mA
Digital inputs, nominal value for True	≥ 15 VDC
Digital inputs, nominal value for False	≤ 5 VDC
Digital inputs, electrical isolation	Yes, via optocoupler
Digital inputs, status display	LED optionally in the plug
Digital inputs, permissible connector cable length	30 m
Digital outputs, number	16
Digital outputs, contact	Transistor
Digital outputs, output voltage	24 VDC
Digital outputs, output current	400 mA
Digital outputs, group current	3,2 A
Digital outputs, electrical isolation	Yes, via optocoupler
Digital outputs, electrical isolation in groups	Yes, in groups of up to 8
Digital outputs, switching frequency	max. 1 kHz
Digital outputs, short-circuit proof	evet
Digital outputs, overload proof	evet
Digital outputs, resistant to low-resistance loads	Yes, up to 5 W
Digital outputs, status display	LED optionally in the plug

Özellik	Değer
Serial interface, number	2
Serial interface, COM / EXT attributes	TTL level, no electrical isolation
Serial interface, connection technology	2x RJ12-Burç
Serial interface, used as RS 232C	SM14 or SM15 required
Serial interface, used as universal interface: EXT	300...115000 Bd 7N1, 7E1, 7O1, 8N1, 8E1, 8O1
SAC plug, required number of plugs	7
Ethernet, connector plug	RJ45
Ethernet, number	1
Ethernet, bus interface	IEEE802.3 (10Base T)
Ethernet, data transmission speed	10 Mbit/s
Ethernet, supported protocols	TCP/IP, EasyIP, http
Programming, language	AWL, KOP
Programming, operating language	DE, EN
Programming, number of programs and tasks per project	64
Programming, number of registers (words)	256
Programming, number of markers	10000
Programming, number of timers (status, actual value, setpoint)	256
Programming, number of counters (status, actual value, setpoint)	256
Programming, support for C/C++	evet
Programming, file handling support	evet
CE mark (see declaration of conformity)	to EU directive for EMC