



Technical data





- Main catalogue
on CD-ROM
or
- www.festo.com



Solenoid valves MZH, Micro pneumatic; MYH, Mini pneumatic

FESTO

Product range overview

Function	Version	Type	Nominal flow rate [l/min]	Pneumatic connection	Operating voltage [V DC]
3/2-way valves	Solenoid valve – Micro pneumatic				
		MZH-3-0,4...	4.0	0.4 mm	24
		MZH-3-...	80	M3	
				1.5 mm	
	MOZH-3-...	80	M3		
			1.5 mm		
	Solenoid valve – Mini pneumatic				
		MYH-3-0,9...	20	0.9 mm	24
		MYH-3-...	190	M5	
			2.3 mm		
MOYH-3-...		170	M5		
		2.3 mm			

Function	Version	Type	Nominal flow rate [l/min]	Pneumatic connection	Operating voltage [V DC]
5/2-way valves	Solenoid valve – Micro pneumatic				
		MZH-5/2...	80	M3	24
				1.5 mm	
	Solenoid valve – Mini pneumatic				
		MYH-5/2...	190	M5	24
			180	2.3 mm	
	Double solenoid valve – Micro pneumatic				
		JMZH-5/2...	80	M3	24
				1.5 mm	
	Double solenoid valve – Mini pneumatic				
		JMYH-5/2...	190	M5	24
			180	2.3 mm	

Function	Version	Type	Nominal flow rate [l/min]	Pneumatic connection	Operating voltage [V DC]	
5/3-way valves	Solenoid valve – Micro pneumatic					
		MZH-5/3G...	40	M3	24	
				1.5 mm		
		MZH-5/E...	40	M3		
			1.5 mm			
	Solenoid valve – Mini pneumatic					
		MYH-5/3G...	130	M5		24
			125	2.3 mm		
MYH-5/E...		130	M5			
		125	2.3 mm			

Solenoid valves MZH, Micro pneumatic; MYH, Mini pneumatic

Product range overview

Type	Semi in-line valve	Sub-base valve	Normal position		Type of pilot control		→ Page
			Closed	Open	Direct	Piloted	
Solenoid valve – Micro pneumatic							
MZH-3-0,4...	-	■	-	-	■	-	2 / 3.5-4
MZH-3-...	■	-	■	-	-	■	2 / 3.5-4
	-	■					
MOZH-3-...	■	-	-	■	-	■	2 / 3.5-4
	-	■					
Solenoid valve – Mini pneumatic							
MZH-3-0,4...	-	■	-	-	■	-	2 / 3.5-5
MZH-3-...	■	-	■	-	-	■	2 / 3.5-5
	-	■					
MOZH-3-...	■	-	-	■	-	■	2 / 3.5-5
	-	■					

Type	Semi in-line valve	Sub-base valve	Type of pilot control		→ Page
			Direct	Piloted	
Solenoid valve – Micro pneumatic					
MZH-5/2...	■	-	-	■	2 / 3.5-4
	-	■			
Solenoid valve – Mini pneumatic					
MYH-5/2...	■	-	-	■	2 / 3.5-5
	-	■			
Double solenoid valve – Micro pneumatic					
JMZH-5/2...	■	-	-	■	2 / 3.5-4
	-	■			
Double solenoid valve – Mini pneumatic					
JMYH-5/2...	■	-	-	■	2 / 3.5-5
	-	■			

Type	Semi in-line valve	Sub-base valve	Type of pilot control		→ Page
			Direct	Piloted	
Solenoid valve – Micro pneumatic					
MZH-5/3G...	■	-	-	■	2 / 3.5-4
	-	■			
MZH-5/E...	■	-	-	■	2 / 3.5-4
	-	■			
Solenoid valve – Mini pneumatic					
MYH-5/3G...	■	-	-	■	2 / 3.5-5
	-	■			
MYH-5/E...	■	-	-	■	2 / 3.5-5
	-	■			

Solenoid valves MZH, Micro pneumatic

Ordering data



Micro pneumatic					
Circuit symbol	Description	Semi in-line valve	Sub-base valve	Part No.	Type
3/2-way valves					
	Type of pilot control: direct Moulded-in cable, 0.3 m	–	■	30 210	MZH-3-04-K
	Type of pilot control: direct Switching status display with LED	–	■	30 217	MZH-3-0,4-LED
	Normally closed	■	–	30 192	MZH-M3-L-LED
	Type of pilot control: piloted	–	■	30 218	MZH-3-1,5-L-LED
	Switching status display with LED				
	Normally open	■	–	30 193	MOZH-3-M3-LED
	Type of pilot control: piloted	–	■	30 219	MOZH-3-1,5-L-LED
	Switching status display with LED				
5/2-way valves					
	Type of pilot control: piloted	■	–	30 194	MZH-5/2-M3-L-LED
	Switching status display with LED	–	■	30 195	MZH-5/2-1,5-L-LED
5/2-way valves – Double solenoid valves					
	Type of pilot control: piloted	■	–	30 195	JMZH-5/2-M3-L-LED
	Switching status display with LED	–	■	30 221	JMZH-5/2-1,5-L-LED
5/3-way valves					
	Normally closed	■	–	30 196	MZH-5/2G-M3-L-LED
	Type of pilot control: piloted	–	■	30 222	MZH-5/2G-1,5-L-LED
	Switching status display with LED				
	Normally exhausted	■	–	30 197	MZH-5/2E-M3-L-LED
	Type of pilot control: piloted	–	■	30 223	MZH-5/2E-1,5-L-LED
	Switching status display with LED				

Solenoid valves MYH, Mini pneumatic











Ordering data

Mini pneumatic					
Circuit symbol	Description	Semi in-line valve	Sub-base valve	Part No.	Type
3/2-way valves					
	Type of pilot control: direct	–	■	34 300	MYH-3-0,9-LED
	Switching status display with LED				
	Normally closed	■	–	34 307	MYH-3-M5-L-LED
	Type of pilot control: piloted	–	■	34 301	MYH-3-2,3-L-LED
	Switching status display with LED				
	Normally open	■	–	34 308	MOYH-3-M5-L-LED
	Type of pilot control: piloted	–	■	34 302	MOYH-3-2,3-L-LED
	Switching status display with LED				
5/2-way valves					
	Type of pilot control: piloted	■	–	34 309	MYH-5/2-M5-L-LED
	Switching status display with LED	–	■	34 303	MYH-5/2-2,3-L-LED
	Switching status display with LED				
5/2-way valves – Double solenoid valves					
	Type of pilot control: piloted	■	–	34 310	JMYH-5/2-M5-L-LED
	Switching status display with LED	–	■	34 304	JMYH-5/2-2,3-L-LED
	Switching status display with LED				
5/3-way valves					
	Normally closed	■	–	34 311	MYH-5/3G-M5-L-LED
	Type of pilot control: piloted	–	■	34 305	MYH-5/3G-2,3-L-LED
	Switching status display with LED				
	Normally exhausted	■	–	34 312	MYH-5/3E-M5-L-LED
	Type of pilot control: piloted	–	■	34 306	MYH-5/3E-2,3-L-LED
	Switching status display with LED				

Solenoid valves MZH, Micro pneumatic

Accessories












Ordering data				
Designation	Brief description	Part No.	Type	
Sub-base, ports on side				
	for 3/2-way valves	Type of pilot control: direct	34 350	AS-MZ-3-M3
		Type of pilot control: piloted	34 351	AS-MZ-3-M5
	for 5/2- and 5/3-way valves		34 352	AS-MZ-5-M5
Manifold for 3/2-way sub-base valves; type of pilot control: direct				
	for 2 valves		30 224	PRMZ-3-M3-2
	for 4 valves		30 226	PRMZ-3-M3-4
	for 6 valves		30 228	PRMZ-3-M3-6
	for 8 valves		30 230	PRMZ-3-M3-8
	for 10 valves		30 232	PRMZ-3-M3-10
Blanking plate for unused positions, 3/2-way				
			32 607	PRMZB-3
Manifold for 3/2-, 5/2- and 5/3-way semi in-line valves; type of pilot control: piloted				
	for 2 valves		30 233	PRMZ-5-M3-2
	for 4 valves		30 235	PRMZ-5-M3-4
	for 6 valves		30 237	PRMZ-5-M3-6
	for 8 valves		30 239	PRMZ-5-M3-8
	for 10 valves		30 241	PRMZ-5-M3-10
Manifold for 3/2-, 5/2- and 5/3-way sub-base valves; type of pilot control: piloted				
	for 2 valves		30 242	PRMZ-5-M5-2
	for 4 valves		30 244	PRMZ-5-M5-4
	for 6 valves		30 246	PRMZ-5-M5-6
	for 8 valves		30 248	PRMZ-5-M5-8
	for 10 valves		30 250	PRMZ-5-M5-10
Blanking plate for unused positions, 5/2- and 5/3-way				
			33 008	PRMZB-5
Plug socket with cable				
	24 V DC, cable length 0.5 m		34 347	KMY-1-24-0,5
	24 V DC, cable length 2.5 m		30 446	KMYZ-1-24-2,5
	24 V DC, cable length 5 m		30 447	KMYZ-1-24-5
	24 V DC, cable length 15 m		193 454	KMYZ-1-24-15
Plug socket				
	for MY and MZ valves		34 345	MSSD-MY
	Crimp connectors (10 pcs.)		34 346	MSSD-MY-C

Solenoid valves MYH, Mini pneumatic

Accessories

FESTO

Ordering data			
Designation	Brief description	Part No.	Type
Sub-base, ports on side			
	for 3/2-way valves	Type of pilot control: direct	34 313 AS-MY-3-M3
		Type of pilot control: piloted	34 314 AS-MY-3-1/8
	for 5/2- and 5/3-way valves		34 315 AS-MZ-5-1/8
Manifold for 3/2-way sub-base valves; type of pilot control: direct			
	for 2 valves		30 316 PRMY-3-M5-2
	for 4 valves		30 318 PRMY-3-M5-4
	for 6 valves		30 320 PRMY-3-M5-6
	for 8 valves		30 322 PRMY-3-M5-8
	for 10 valves		30 324 PRMY-3-M5-10
Blanking plate for unused positions, 3/2-way			
		34 343	PRMYB-3
Manifold for 3/2-, 5/2- and 5/3-way semi in-line valves; type of pilot control: piloted			
	for 2 valves		34 325 PRS-M5-2
	for 4 valves		34 327 PRS-M5-4
	for 6 valves		34 329 PRS-M5-6
	for 8 valves		34 331 PRS-M5-8
	for 10 valves		34 333 PRS-M5-10
Manifold for 3/2-, 5/2- and 5/3-way sub-base valves; type of pilot control: piloted			
	for 2 valves		34 334 PRMY-5-1/8-2
	for 4 valves		34 336 PRMY-5-1/8-4
	for 6 valves		34 338 PRMY-5-1/8-6
	for 8 valves		34 340 PRMY-5-1/8-8
	for 10 valves		34 342 PRMY-5-1/8-10
Blanking plate for unused positions, 5/2- and 5/3-way			
		34 344	PRMYB-5
Plug socket with cable			
	24 V DC, cable length 0.5 m		34 347 KMY-1-24-0,5
	24 V DC, cable length 2.5 m		30 446 KMYZ-1-24-2,5
	24 V DC, cable length 5 m		30 447 KMYZ-1-24-5
	24 V DC, cable length 15 m		193 454 KMYZ-1-24-15
Plug socket			
 	for MY and MZ valves		34 345 MSSD-MY
	Crimp connectors (10 pcs.)		34 346 MSSD-MY-C

