

Flow Control Valves – Inch Series

Quick Star Flow/Pressure Controls

One-way Flow Control Valve, In-line
Housing: Polymer
Seal: NBR



| Ordering Data | | | | | |
|---------------|-----------|------------------------|---------------------------|------------------|-----|
| Part No. | Type | Function ¹⁾ | For Tubing O.D. D1 [inch] | Wrench Size [mm] | |
| | | | | WS1 | WS2 |
| 192754 | GR-QS-1/4 | A or Z | 1/4 | 8 | 13 |
| 192755 | GR-QS-3/8 | A or Z | 3/8 | 8 | 13 |
| 192756 | GR-QS-1/2 | A or Z | 1/2 | 8 | 14 |

Retainer for One-way Flow Control Valves



| Ordering Data | | |
|---------------|-------------|------------------------|
| Part No. | Type | For Tubing O.D. [inch] |
| 195495 | GR-H-QS-3-4 | 1/4 |
| 195496 | GR-H-QS-6-8 | 3/8 |

One-way Flow Control Valve, UNF, with Elbow Connector, Knurled Screw, and Locknut
Housing: Polymer
Seal: NBR



| Ordering Data | | | | | |
|---------------|--------------------------|------------------------|----------|---------------------------|--------------------|
| Part No. | Type | Function ¹⁾ | Thread C | For Tubing O.D. D1 [inch] | Wrench Size [inch] |
| 165008 | GRLA-10-32-UNF-QS-5/32-U | A | 10-32 | 5/32 | 5/16 |
| 192753 | GRLA-10-32-UNF-QS-1/4-U | A | 10-32 | 1/4 | 5/16 |

One-way Flow Control Valve, NPT, with Elbow Connector, Knurled Screw, and Locknut
Housing: Polymer
Seal: NBR



| Ordering Data | | | | | |
|---------------|-------------------------|------------------------|----------|---------------------------|--------------------|
| Part No. | Type | Function ¹⁾ | Thread C | For Tubing O.D. D1 [inch] | Wrench Size [inch] |
| 192858 | GRLA-1/16-NPT-QS-3/16-U | A | 1/16 | 3/16 | 7/16 |
| 192859 | GRLA-1/16-NPT-QS-1/4-U | A | 1/16 | 1/4 | 7/16 |
| 165009 | GRLA-1/8-NPT-QS-5/32-U | A | 1/8 | 5/32 | 7/16 |
| 190941 | GRLA-1/8-NPT-QS-3/16-U | A | 1/8 | 3/16 | 7/16 |
| 165010 | GRLA-1/8-NPT-QS-1/4-U | A | 1/8 | 1/4 | 7/16 |
| 165013 | GRLA-1/8-NPT-QS-5/16-U | A | 1/8 | 5/16 | 7/16 |
| 190944 | GRLA-1/8-NPT-QS-5/16-U | A | 1/4 | 3/16 | 9/16 |
| 165011 | GRLA-1/4-NPT-QS-1/4-U | A | 1/4 | 1/4 | 9/16 |
| 165014 | GRLA-1/4-NPT-QS-5/16-U | A | 1/4 | 5/16 | 9/16 |
| 190947 | GRLA-1/4-NPT-QS-3/8-U | A | 1/4 | 3/8 | 9/16 |
| 165012 | GRLA-3/8-NPT-QS-1/4-U | A | 3/8 | 1/4 | 3/4 |
| 165015 | GRLA-3/8-NPT-QS-5/16-U | A | 3/8 | 5/16 | 3/4 |
| 190950 | GRLA-3/8-NPT-QS-3/8-U | A | 3/8 | 3/8 | 3/4 |
| 190951 | GRLA-3/8-NPT-QS-1/2-U | A | 3/8 | 1/2 | 3/4 |
| 190952 | GRLA-1/2-NPT-QS-3/8-U | A | 1/2 | 3/8 | 1 |
| 190953 | GRLA-1/2-NPT-QS-1/2-U | A | 1/2 | 1/2 | 1 |

1) Function:
 A = Control of Exhaust air
 Z = Control of Supply air
 O = Flow control in both directions

* Packaged in quantities of 10. (No asterisk = items sold by the unit.)
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.