



- Up to 12 outlets
- Supply line optionally left or right

Distribution manifolds FR

Product range overview

FESTO

Series	Design	Type	Pneumatic connection		Number of		→ Page/ Internet
			Supply line	Outlet	Supply lines	Outlets	
	Manifold with 4 connections						
		FR-4	G1/8	G1/8	1	4	3
			G1/4	G1/4			
			G3/8	G3/8			
			G1/2	G1/2			
	Manifold with 8 connections						
		FR-8	G3/8	G1/8	1	8	3
			G1/2	G1/4			
			G3/4	G1/2			
	Manifold with 9 connections						
		FR-9	G1/8	M3	1	9	4
	Manifold with 12 connections						
		FR-12	G1/8	M5	1	12	4

Distribution manifolds FR

Technical data

FESTO

Distribution manifold FR-4


No. of supply lines: 1

No. of outlets: 3

Operating pressure: 0 ... 16 bar

Material:

Die-cast aluminium



Dimensions and ordering data														
Connection D1		B1	B2	B3	D5	H1	L1	L2	L3	L4	Weight [g]	Part No.	Type	PU*
Supply line	Outlet													
G1/8	G1/8	20	11.6	13	4.4	17	56	13.5	17	46	25	6 701	FR-4-1/8-B	1
G1/4	G1/4	28	17	16	6.4	30	89	20	29	74	60	7 849	FR-4-1/4-C	1
G3/8	G3/8	32	19	20	6.4	26	85	20	26	72	75	6 703	FR-4-3/8-B	1
G1/2	G1/2	38	22	25	6.4	32	105	25	32	90	120	6 704	FR-4-1/2-B	1

* Packaging unit quantity

Distribution manifold FR-8


No. of supply lines: 2, including one sealed with a blanking plug

No. of outlets: 8

Operating pressure: 0 ... 16 bar

Material:

Die-cast aluminium



Dimensions and ordering data																
Connection D1	Connection D2	B1	B2	D5 Ø	D6 Ø	H1	H2	H3	L1	L2	L3	L4	Weight [g]	Part No.	Type	PU*
Supply line	Outlet															
G3/8	G1/8	40	26	11	6.6	30	15	6.8	114	22.5	23	100	135	2 077	FR-8-1/8	1
G1/2	G1/4	50	34	11	6.6	35	17.5	6.8	144	24	32	128	230	2 078	FR-8-1/4	1
G3/4	G1/2	60	40	15	6.6	45	22.5	9	170	31	36	150	1000	6 411	FR-8-1/2	1

* Packaging unit quantity

Distribution manifolds FR

Technical data

FESTO

Distribution manifold FR-9


No. of supply lines: 1

No. of outlets: 9

Operating pressure: 0 ... 16 bar

Material:

Anodised aluminium



Dimensions and ordering data				
Connection		Weight [g]	Part No.	Type
Supply line	Outlet			
G1/8	M3	15	30 981	FR-9-M3-B
				PU*

* Packaging unit quantity

Distribution manifold FR-12


No. of supply lines: 2, including one sealed with a blanking plug

No. of outlets: 12

Operating pressure: 0 ... 16 bar

Material:

Anodised aluminium



Dimensions and ordering data				
Connection		Weight [g]	Part No.	Type
Supply line	Outlet			
G1/8	M5	40	4 525	FR-12-M5
				PU*

* Packaging unit quantity