

Connecting cables NEBV, for valves

Technical data

Plug socket with cable KMPPE

- Plug socket with cable for proportional pressure regulators MPPE and MPPES
- Pre-assembled
- Cable lengths 2.5 and 5 m



General technical data	
Electrical connection	Angled socket, 8-pin, M16
Nominal operating voltage [V DC]	24
Cable composition [mm ²]	8x0.25
Cable diameter [mm]	6.8
Type of mounting	M16x0.75 union nut
Mounting position	Any

Materials	
Pin contact	Bronze
Cable sheath	PVC

Operating and environmental conditions	
Ambient temperature [°C]	-30 ... +80

Circuitry (socket view)		
Socket	Pin	Wire colour
	1	White
	2	Brown
	3	Green
	4	Yellow
	5	Grey
	6	Pink
	7	Red
	8	Blue

Dimensions Download CAD data → www.festo.com

1 PVC cable

Ordering data				
Electrical connection	Product weight [g]	Length [m]	Part No.	Type
Angled socket, 8-pin, M16	243	2.5	161879	KMPPE-B-2,5
	459	5	161878	KMPPE-B-5