

AS-interface® modules CACF

Technical data

CACF-BT-AS
AS-interface module as bus termination

The passive bus termination enables the maximum permissible AS-interface cable length to be extended to approx. 200 m.
A maximum of one component per AS-interface can be used for extending the cable.




General technical data		
Connection technology		AS-interface flat cable/AS-interface round cable
Status displays		Yellow LED AS-interface voltage > 18.5 V Green LED AS-interface voltage > 26 V
Operating voltage	[V DC]	30 (AS-interface voltage)
Current consumption	[mA]	10
Protection class		IP65
Dimensions W x L x H	[mm]	46 x Ø19
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant

Operating and environmental conditions		
Ambient temperature	[°C]	0 ... +55
Storage temperature	[°C]	-25 ... +75
Certification		cULus listed (OL) C-Tick
CE mark (see declaration of conformity) ¹⁾		In accordance with EU EMC Directive

1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com → Support → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Dimensions Download CAD data → www.festo.com



Type	D1 Ø	L1
CACF-BT-AS	19	46

Ordering data		Part No.	Type
	AS-interface module as bus termination	567035	CACF-BT-AS