

Plug connectors NECV for valves, for self-assembly

Technical data

Plug socket MSSD-ZBZC

- For valves with ZB and ZC solenoid coils



General technical data	
Electrical connection	Socket 2-pin
Nominal operating voltage [V DC]	24
Operating voltage range [V DC]	3 ... 36
Connection cross section [mm ²]	0.22 ... 0.34
Type of mounting	Self-tapping central screw
Mounting position	Any
Protection class to EN 60529	IP40 (assembled)

Materials	
Housing	PA
Note on materials	RoHS-compliant

Operating and environmental conditions	
Ambient temperature [°C]	-10 ... +50
Certification	Germanischer Lloyd

Dimensions Download CAD data → www.festo.com

- 1 Mounting screw
- 2 Inscription label IBS-6x10
- 4 Pin allocations for ZB solenoid coil
- 5 Pin allocations for ZC solenoid coil

Ordering data			
Description	Weight	Part No.	Type
Plug socket for valves with ZB and ZC solenoid coils	11 g	185521	MSSD-ZBZC