


Distributors NEDV for valves

Technical data

Connecting cable NEDV-L2R1-V7





- Connecting cable for VPWP valves
- Pre-assembled
- 0.2 m cable length
- For connection to sub-base VAPB-S3



General technical data	
Electrical connection	2x angled sockets, M12, 3-pin One angled plug, M8, 4-pin
Based on standard	EN 61076-2-101, EN 61076-2-104, EN 61984
Cable composition [mm ²]	2x0.14
Cable diameter [mm]	2.9
Cable length [m]	0.2
Operating voltage range [DC V]	0 ... 30
Acceptable current load [A]	2
Mounting position	Any
Protection class to EN 60529	IP65

Materials	
Cable sheath	TPE-U (PUR)
Note on materials	RoHS-compliant

Operating and environmental conditions	
Ambient temperature [°C]	-25 ... +80


Circuitry (socket/plug view)		
Socket	Circuitry	Socket
		
		

Distributors NEDV for valves

Technical data

Dimensions

Download CAD data → www.festo.com



- 1 Plug M8, 4-pin
- 2 Socket M12, 3-pin

Type	D1 ∅	D2	D3 ∅	D4	D5 ∅	H1	H2	L1	L2	L3	L4
NEDV-L2R1-V7-M12W3-K-0.1L1-N-M8W4-0.2R1	2.9	M8	9.6	M12	15	24	26	200	26.9	37.5	100

Ordering data

Electrical connection	Product weight [g]	Length [m]	Part No.	Type
<ul style="list-style-type: none"> • 2x angled sockets, M12, 3-pin • One angled plug, M8, 4-pin 	28	0.2	2384165	NEDV-L2R1-V7-M12W3-K-0.1L1-N-M8W4-0.2R1