

Electrical connection technology, for AS-interface

Technical data – KASI

- Addressing cable for any slaves including
 - Individual valve interface
 - CP valve terminals
- Cable length 2.5 m
- Pre-assembled
- Reverse polarity protected



General technical data		
Type	KASI-ADR	
Connection type	Plug-in/screw-in	
Connection cross-section	[mm ²]	2x 1.5
Protection class	IP65	
Material of plug, straight	Housing	PBT
	Contacts	Copper base alloy
	Union nut	PBT
Material of plug, angled	Housing	PUR
	Contacts	Bronze
	Union nut	Nickel-plated brass
Material of flat cable socket	Housing	PA
	Contacts	Bronze
Material of cable sheath	Rubber compound	
Ambient temperature	[°C]	-40 ... +85

Ordering data						
View	Electrical connection	Operating voltage range		Current-carrying capacity	Part No.	Type
		[V AC]	[V DC]	[A]		
	<ul style="list-style-type: none"> • Plug, straight, 4-pin • Plug, angled, 4-pin • Socket, straight, 2-pin 	60	75	3	18960	KASI-ADR

Dimensions

Download CAD data → www.festo.com

- 1 Round plug connector for connection to addressing device
- 2 Flat cable socket for connecting stations in the AS-interface network with plug-in connection
- 3 Flat cable socket with M12 connection plug for stations in the AS-interface network with M12 interface