

Electrical connection technology, for inputs/outputs

Technical data – KVIA-...

- Plug socket with cable for inputs/ outputs
- Pre-assembled at both ends
- Cable lengths 5 m or 10 m
- 4-pin/5-pin
- Round plug
- Suitable for chain link trunking



General technical data	
Type	KVIA-...
Type of mounting	M16/M12 union nut
Mounting position	Any
Operating voltage range	[V AC] Max. 250
Current-carrying capacity	[A] 1
Protection class to EN 60 529	IP65 (assembled)
Material of housing	PBT
Material of contacts	Silver-plated/gold-plated bronze
Material of cable sheath	PVC
Ambient temperature	[°C] -30 ... +80

Ordering data								
	Suitable for chain link trunking	Electrical connection	Constructional design [mm ²]	Cable diameter [mm]	Product weight [g]	Cable length [m]	Type	Part No.
	■	Straight plug	6x0.25	8	306	5	KVIA-5	163960
	■	Straight plug	6x0.25	8	567	10	KVIA-10	163961
	■	Straight plug Straight socket	4x0.25	6.2	297	5	KVIA-MPYE-5	161984
	■	Straight plug Straight socket	4x0.25	6.2	530	10	KVIA-MPYE-10	161985
	■	Straight plug Angled socket	6x0.25	8	352	5	KVIA-MPPE-5	163882
	■	Straight plug Angled socket	6x0.25	8	828	10	KVIA-MPPE-10	163883


Electrical connection technology, for inputs/outputs

Technical data – KVIA-...

Dimensions


Download CAD data → www.festo.com

KVIA-5 and KVIA-10




1 Cable length 5 m or 10 m

Type KVIA-MPPE-...



1 Cable length 5 m or 10 m






Type KVIA-MPYE-...



1 Cable length 5 m or 10 m

Electrical connection technology, for inputs/outputs

Technical data – KVIA-...

Wiring allocation (socket/plug view)				
KVIA-5 and KVIA-10				
Plug	Pin	Core colour		
	1	Grey		
	2	Pink		
	3	Green		
	4	Yellow		
	5	Brown		
	6	White		
	Housing		Screen	
Type KVIA-MPPE-...				
Plug	Pin	Core colour	Pin	Socket
	1	Grey	6	
	2	Pink	8	
	3	Green	4	
	4	Yellow	2	
	5	Brown	7	
	6	White	3	
	Housing		Screen	
Type KVIA-MPYE-...				
Plug	Pin	Core colour	Pin	Socket
	1	-	-	
	2	-	-	
	3	Green	3	
	4	Yellow	4	
	5	Brown	1	
	6	White	2	
	Housing		Screen	

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com