FESTO

Electrical adapters NEFU, universal Technical data

Control cabinet through-hole NEFU-D12G4

• Control cabinet through-hole for Ethernet connecting cables with M12 connection



General technical data


General technical data							
Туре		NEFU-D12G4-D12DG4	NEFU-D12G4-R3DW4				
Electrical connection 1		Straight socket, 4-pin, M12x1, D-coded	Straight socket, 4-pin, M12x1, D-coded				
Electrical connection 2		Straight socket, 4-pin, M12x1, D-coded	Angled socket, 4-pin, RJ45				
Conforms to standard		EN 61076-2-101	EN 61076-2-101				
		-	IEC 60603-7-3				
Transmission characteristics		In accordance with category 5, EN 50173, class D					
		In accordance with category 5, ISO/IEC 11801, class D					
Operating voltage range	[V DC]	0 30					
Surge resistance	[kV]	0.8					
Acceptable current load at [A]		4	2				
40°C							
Type of mounting		Screw-clamped					
Nominal tightening torque	[Nm]	0.5 (for plug connector M12x1)					
	[Nm]	2.5 (hex nut for mounting in control cabinet)					
Degree of protection to EN 60529		-	IP20				
		IP65	IP65				
		IP67	IP67				

Materials					
Туре	NEFU-D12G4-D12DG4	NEFU-D12G4-R3DW4			
Housing	Nickel-plated brass	PA, nickel-plated brass, die-cast zinc			
Housing colour	Silver	Black			
Pin contacts	Gold-plated brass	Gold-plated brass			
Note on materials	RoHS compliant	RoHS compliant			
	Free of copper and PTFE	Free of copper and PTFE			
	Contains PWIS (paint-wetting impairment substances)	-			

Operating and environmental conditions					
Туре	NEFU-D12G4-D12DG4	NEFU-D12G4-R3DW4			
Ambient temperature [°C]	-25 +85	-5 +60			
Degree of contamination	3	3			

Electrical adapters NEFU, universal Technical data

FESTO





Туре	B1	D1	D2	D3	D4	H1	L1	L2	L3	=© 1	=© 2
NEFU-D12G4-D12DG4	-	M16x1.5	13.5	13.5	M12x1	-	43.2	14.6	10	SW17	SW14
NEFU-D12G4-R3DW4	23	M16x1.5	M12x1	-	-	30.7	40.1	23.1	-	SW18	-
Mounting aperture	13.8	16	-	-	-	-	-	-	-	-	-

Ordering data				
	Electrical connection 1	Electrical connection 2	Part No.	Туре
	Straight socket, 4-pin, M12x1, D-coded	Straight socket, 4-pin, M12x1, D-coded	8040459	NEFU-D12G4-D12DG4
		Angled socket, 4-pin, RJ45	8040457	NEFU-D12G4-R3DW4