


Distributors NEDV for valves

Technical data



Connecting cable NEDV-L2R1-V7

- Connecting cable for VPWP valves
- Pre-assembled
- 0.2 m cable length
- For connection to sub-base VAPB-S3



General technical data	
Electrical connection	2x angled sockets, M12, 3-pin One angled plug, M8, 4-pin
Based on standard	EN 61076-2-101, EN 61076-2-104, EN 61984
Cable composition	[mm ²] 2x0.14
Cable diameter	[mm] 2.9
Cable length	[m] 0.2
Operating voltage range	[DC V] 0 ... 30
Acceptable current load	[A] 2
Mounting position	Any
Protection class to EN 60529	IP65

Materials	
Cable sheath	TPE-U (PUR)
Note on materials	RoHS-compliant

Operating and environmental conditions	
Ambient temperature	[°C] −25 ... +80

Circuitry (socket/plug view)		
Socket	Circuitry	Socket


Distributors NEDV for valves

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



- 1 Plug M8, 4-pin
2 Socket M12, 3-pin

Type	D1 Ø	D2	D3 Ø	D4	D5 Ø	H1	H2	L1	L2	L3	L4	⌀C1	⌀C2
NEDV-L2R1-V7-M12W3-K-0.1L1-N-M8W4-0.2R1	2.9	M8x1	10	M12x1	15	24	26	200	26.9	37.5	100	13	9

Ordering data

Electrical connection	Product weight [g]	Length [m]	Part No.	Type
2x angled sockets, M12, 3-pin - One angled plug, M8, 4-pin	28	0.2	2384165	NEDV-L2R1-V7-M12W3-K-0.1L1-N-M8W4-0.2R1