AS-interface® modules CACF

FESTO

1

Technical data

CACF-BT-AS

AS-interface module as bus termination

The passive bus termination enables the maximum permissible AS-interface cable length to be extended to approx. 200 m.

A maximum of one component per AS-interface can be used for extending the cable.



General technical data				
Connection technology		AS-interface flat cable/AS-interface round cable		
Status displays		Yellow LED AS-interface voltage > 18.5 V		
		Green LED AS-interface voltage > 26 V		
Operating voltage	[V DC]	30 (AS-interface voltage)		
Current consumption	[mA]	10		
Protection class		IP65		
Dimensions W x L x H	[mm]	46 x Ø19		
Note on materials		Contains PWIS (paint-wetting impairment substances)		
		RoHS-compliant		

Operating and environmental conditions					
Ambient temperature	[°C]	0 +55			
Storage temperature	[°C]	-25 +75			
Certification		cULus listed (OL)			
		C-Tick			
CE mark (see declaration of conformity) ¹⁾		In accordance with EU EMC Directive			

1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com Support Support User documentation.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Dimensions	Download CAD data → www.festo.com
L1 5	

Туре	D1 Ø	L1
CACF-BT-AS	19	46

Ordering data						
		Part No.	Туре			
	AS-interface module as bus termination	567035	CACF-BT-AS			