

Plug connectors for self-assembly, M16, 8-pin

FESTO

Technical data

Plug socket MPPE

- For proportional pressure regulators MPPES



General technical data		
Electrical connection		Angled socket
		8-pin
		Solderable
Operating voltage range	[V DC]	Max. 60
Acceptable current load	[A]	5
Cable connector		Pg9
Permissible cable diameter	[mm]	6 ... 8
Connection cross section	[mm ²]	Max. 0.75
Connection frequency		500
Type of mounting		M16x0.75 union nut
Mounting position		Any
Protection class to EN 60529		IP67 (assembled)

Materials	
Housing	PA
Housing colour	Black
Union nut	PA
Pin contacts	Tin-plated copper

Operating and environmental conditions	
Ambient temperature	[°C] -30 ... +95

Dimensions	Download CAD data → www.festo.com
MPPE-3-B	Pin allocation

Ordering data			
Description	Weight	Part No.	Type
Plug socket for proportional pressure regulators MPPES	65 g	161839	MPPE-3-B

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalneptla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us

   

www.festo.com/socialmedia



www.festo.com

Subject to change