

Plug connectors NECV for valves, for self-assembly

Technical data

Plug socket MSSD-ZBZC

- For valves with ZB and ZC solenoid coils



General technical data	
Electrical connection	Socket
	2-pin
Nominal operating voltage [V DC]	24
Operating voltage range [V DC]	3 ... 36
Connection cross section [mm ²]	0.22 ... 0.34
Type of mounting	Self-tapping central screw
Mounting position	Any
Protection class to EN 60529	IP40 (assembled)

Materials	
Housing	PA
Note on materials	RoHS-compliant

Operating and environmental conditions	
Ambient temperature [°C]	-10 ... +50
Maritime classification ¹⁾	See certificate

1) Additional information www.festo.com/sp → Certificates.

Dimensions Download CAD data → www.festo.com

1 Mounting screw
2 Inscription label IBS-6x10
4 Pin allocations for ZB solenoid coil
5 Pin allocations for ZC solenoid coil

Ordering data			
Description	Weight	Part No.	Type
Plug socket for valves with ZB and ZC solenoid coils	11 g	185521	MSSD-ZBZC

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center
Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepantla,
Estado de México

Multinational Contact Center
01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center
1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change