

Electrical connection technology, for individual connection

Technical data – KMH

- Plug socket with cable for the horizontal connection of individual valves
- Pre-assembled
- Cable lengths 0.5 m, 1 m, 2.5 m or 5 m
- 3-pin plug socket
- Not suitable for chain link trunking



General technical data	
Electrical connection	3-pin plug socket
Type of mounting	Clip
Mounting position	Any
Operating voltage [V]	60 DC
Current-carrying capacity [A]	3
Cable diameter [mm]	1.3
Protection class to EN 60 529	IP40
Material of housing	POM
Material of contacts	Tin-plated bronze
Material of cable sheath	PVC
Ambient temperature [°C]	-40 ... +105

Dimensions Download CAD data → www.festo.com

1 Pin 1, core colour black
 2 Pin 2, core colour blue
 3 Pin 3, core colour red
 L1 Length according to type
 (0.5 m, 1 m, 2.5 m or 5 m)

Ordering data					
	Constructional design [mm ²]	Product weight [g]	Cable length (L1) [m]	Part No.	Type
	3x0.14	6	0.5	527396	KMH-D-0,5
	3x0.14	11	1	527397	KMH-D-1
	3x0.14	24	2.5	527398	KMH-D-2,5
	3x0.14	46	5	527399	KMH-D-5