

# Plug connectors NECV for valves, for self-assembly

Technical data

**Plug socket MSSD-N**

- For valves with MD-2 and MH-2 solenoid coils



General technical data	
Electrical connection	Angled socket
	3-pin
	Screw terminal
	Square design MSF
	To EN 175301-803
Cable connector	M20
Permissible cable diameter [mm]	8 ... 10
Connection cross section [mm <sup>2</sup> ]	Max. 1.5
Type of mounting	M3 central screw
Mounting position	Any
Protection class to EN 60529	IP65 (assembled)

Materials	
Housing	PA reinforced
Housing colour	Black
Screws	Steel
Seals	VMQ
Note on materials	Contains PWIS (paint-wetting impairment substances), RoHS-compliant

Operating and environmental conditions		
Ambient temperature	[°C]	-20 ... +80

**Dimensions** Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

1 Plug pattern to EN 175301-803, type A

Ordering data			
Description	Weight	Part No.	Type
Angled socket, 3-pin, square design MSF	30 g	550067	MSSD-N

# Festo - Your Partner in Automation



**1 Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

**Festo Customer Interaction Center**  
Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)



**2 Festo Pneumatic**  
Av. Ceylán 3,  
Col. Tequesquináhuac  
54020 Tlalnepantla,  
Estado de México

**Multinational Contact Center**  
01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)



**3 Festo Corporation**  
1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

**Festo Customer Interaction Center**  
1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)



**4 Regional Service Center**  
7777 Columbia Road  
Mason, OH 45040

Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)

Subject to change